







P.C.B LAYOUT



Ordering Information:

C3030WR-2xXP - ** - **
1 2 3

1.Part No.

2.Material:

(blank):Nylon 66 UL94V-0

LCP:LCP UL94V-0

GWT:Nylon 66 UL94V-0,GWT 750°C

3.Finish:


(blank):Tin over Nickel

G:Gold over Nickel(1"U)

G3:Gold over Nickel(3"U)

G15:Gold over Nickel(15"U)

G30:Gold over Nickel(30"U)



SPECIFICATIONS:

Current Rating:12.5A AC,DC (AWG #18)

Voltage Rating: 600V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 10mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: 1500V AC/minute

Pin Material: Brass/Tin over Nickel

Material: Nylon 66,UL94V-0(Black)

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2x1P	---	6.65	2x7P	18.00	24.65
2x2P	3.00	9.65	2x8P	21.00	27.65
2x3P	6.00	12.65	2x9P	24.00	30.65
2x4P	9.00	15.65	2x10P	27.00	33.65
2x5P	12.00	18.65	2x11P	30.00	36.65
2x6P	15.00	21.65	2x12P	33.00	39.65

CJTconn

CHANGJIANG CONNECTORS CO.,LTD.

Unit		Scale		Sheet		TITLE			
mm		2:1		1 of 1					
DRWN		CHK'D		APPR		3.00mm PITCH			
Xu Lei		Diankui Wan		Jack Yin					
General Tolerances		THIRD ANGLE PROJECTION		RIGHT-ANGLE DUAL ROW WAFER					
x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°									
				DRAWING NO.				REV	
				C3030WR-2xXP				A2	

A2	CHANGE THE DRAWING	2022.01.17
A1	CHANGE THE Current Rating	2018.12.19
A0	NEW RELEASE	2009.05.10
REV	DESCRIPTION	DATE