






A	B	C	D	E	F
修订 REV: A0	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE	
NEW DWG		2016-03-12			

NOTES:
1. MATERIAL:
HOUSING: NYLON,UL94V-0,COLOR:BLACK;
COVER: PPS,UL94V-0,COLOR:NATURE;
CONTACT: COPPER ALLOY;
2. PLATING:
CONTACT: GOLD OR TIN PLATED ON NICKEL OVERALL.
3. RATING:
CURRENT RATING: 0.4A AC/DC
VOLTAGE RATING: 50V AC/DC
TEMPERATURE RANGE: -30°C~+85°C;
4. PART NO:



15PIN专用



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		APPD* 核准:	TITLE: 产品名称: FPC 1.0间距3.0厚5.5高立贴抽屉式			
X.X	±0.30	X.X*	±3*	PART NO: 产品编号:	1.0K-3.0CT-15PB	
X.XX	±0.20	X.XX*	±2*	CHECK: 校对:	王建业	DATE
X.XXX	±0.10	X.XXX*	±1*	DRAW: 绘图:	黄艳兰	SCALE

2016-03-12 1:1 mm A001