








REV	MARK	修改摘要	签名	日期
NO		NEW DWG		2016-03-12

Note:

1.Material

1.1: Housing: NYLON46 UL94-V0 Color:NATURE.

1.2: Actuator: PPS UL94-V0 Color:NATURE.

1.3: Contact: Phosphor Bronze.

1.4: LEG: Brass.

2.Plating

2.1: Contact: Gold Flash or Tin.

2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

3.1: Operating Voltage: 50V AC/DC.

3.2: Current Rating: 0.4A AC/DC.


3.3: Operating Temperature:-25°C~+85°C.

PORT NO	Dimension				
	A	B	C	D	E
30P	35.20	34.90	29.00	36.60	31.20
26P	31.20	30.90	25.00	32.60	27.20
24P	29.20	28.90	23.00	30.60	25.20
16P	21.20	20.90	15.00	22.60	17.20



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: FPC 1.0间距3.6厚5.75高立贴抽展式

X.X ±0.30 X.X* ±3°

APPD:
核准:

PART NO:
产品编号: 1.0K-3.6CT-nPB

X.XX ±0.20 X.XX* ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX* ±1°

DRAW:
绘图: 黄艳兰

2016-03-12 1:1 mm A001