



- NOTES:
1. RATING: 5A125/250VAC UL CUL VDE CQC.
  2. OPERATING FORCE: 340gf(max)
  3. CONTACT RESISTANCE: <50mΩ
  4. INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
  5. DIELECTRIC STRENGTH: >1500Vac 0.5mA 1 MINUTE
  6. COLOR: BLACK
  7. DEGREE OF PROTECTION: IP67

电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	DRAWING NO. REV.	
5	→	10	→		RANGE				LMC 2019.05.20	SCALE	NO	DRAWING NO.	REV.
4	→	9	→		TOLERANCE			MAT'L		***			
3	→	8	→	X	±0.30			MATERIAL NO.		RTM2-1G4D05C340	*****	A0	
2	→	7	→	X.X	±0.20								
1	→	6	→	X.XX	±0.10								
					±1°	ROCKTEK ELECTRICAL(SHENZHEN) CO.,LTD.							

