

4

3

2

1

D

D

C

C

B






B

A

A

NOTES:

- 1. Rating : 22A GP 125/250VAC 1E4 40T125
 22(6)A 125/250VAC 1E4 40T125
 22A 42VDC 1E4 40T125
- 2. Contact resistance : 50mΩ Max
- 3. Insulation resistance : >100MΩ (Min) 500VDC
- 4. Dielectric strength : >1500VAC 0.5mA 1 minutes



电话: 0769-82310511-867
 邮箱: hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10					RT-M1-0C3B22A200-A		*****	AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.							

4

3

2

1