



④ 面板厚度 X, X^{+0.2}

品名	X, X
RT-C14B-D1+SS11-1BB	0.8mm
RT-C14B-D2+SS11-1BB	1.0mm
RT-C14B-D3+SS11-1BB	1.5mm
RT-C14B-D4+SS11-1BB	2.0mm
RT-C14B-D5+SS11-1BB	3.0mm
RT-C14B-D6+SS11-1BB	1.2mm

Socket : RT-C14B-D**-13-R
 1. Rating : 10A 250VAC (CCC ; UL ; CUL)
 2. Insulation resistance : >100MΩ Min 500VDC
 3. Withstand voltage : >2000VAC 0.5mA 1 minute
 Switch : SS11-BBIWG-R20-R
 1. Rating : 10A 125/250VAC (UL ; CUL)
 12(4)A 250V~ (ENEC17 ; NEMKO ; CQC ; KC)
 2. Contact resistance : <50mΩ
 3. Insulation resistance : >100MΩ Min 500VDC
 4. Dielectric strength : >1500VAC 0.5mA 1 minute

电话 : 0769-82310511-867
 邮箱 : hooya89@hooya.hk

⑤	→	⑩	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
④	→	⑨	→	RANGE	TOLERANCE				LMC	SCALE	NO			
③	→	⑧	→	X	±0.30				2020.12.23	MAT'L	***			
②	→	⑦	→	X.X	±0.20					MATERIAL NO.			DRAWING NO.	REV.
①	→	⑥	→	X.XX	±0.10					RT-C14B-D3+SS11-1BB			*****	AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGIION ELECTRONIC & HARDWARE CO., LTD.								