



NOTES:

- "□" DENOTES CRITICAL DIMENSIONS
- Part name: Outlet
- Power Rating: 15A 250VAC
- Life test: No Load condition: 5,000 cycles
- On Load test:
 - Tested at Over Load condition 150% rated current: 500 cycles.
Check temp rise - not exceed 30°C
 - Tested at On Load condition - rated current 15A: 500 cycles.
Check temp rise - not exceed 30°C
- Terminal pull force 10kg(min)
- Insertion Force: 9±4kg
- Withdrawal Force: 6±3kg

电话: 0769-82310511-867
 邮箱: hooya89@hooya.hk

Part name : Female 4-Poles Connector

2	BODY	PBT 4130(a) 94-V0 Gray Blue E304813	1
1	PIN 1#	C2680 4.8X0.8 Tin-plating 3~5µm	4
NO.	PART NAME	MATERIAL	Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE					SCALE	NO		
3	→	8	→	X	±0.4					MAT'L	***		
2	→	7	→	X.X	±0.3					MATERIAL NO.		DRAWING NO.	REV.
1	修改进胶口	6	→	X.XX	±0.2					RT-C05C-C		WIF111007	B
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	ROCK TEK ELECTRICAL(SHENZHEN) CO., LTD.							

4 3 2 1