





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED	04FEB2021	F.Z	R.B



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



AS SHOWN :
20POS(X-KEY)1-2040516-0

20	X	9	18.0	22.6	GOLD PLATED	1-2040516-0
18	X	8	16.0	20.6	Sn PLATED	3-2040516-9
18	X	8	16.0	20.6	GOLD PLATED	1-2040516-9
10	X	4	8.0	12.6	Sn PLATED	3-2040516-5
10	X	4	8.0	12.6	GOLD PLATED	1-2040516-5
POS	KEY	n	A	B	FINISHED	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3, ±5°

0-PLC	±
1-PLC	±0.5
2-PLC	±0.13
3-PLC	±0.013
4-PLC	±0.0001
ANGLES	±

MATERIAL

FINISH

DWN
M. MAEBASHI
22JUL2008

CHK
T. KUDO
22JUL2008

APVD
S. MANABE
22JUL2008

PRODUCT SPEC
108-78268

APPLICATION SPEC
114-5377

WEIGHT
-

CUSTOMER DRAWING


TE Connectivity

NAME
DYNAMIC D1100D 2.0mmPITCH
HDR ASSY (V-TYPE)
4-20POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2040516	

SCALE 4:1 SHEET 1 OF 3 REV B2


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 3			



ROW ID
BOTH SIDE


CIRCUIT NO
CAVITY MARK
ALPHABET:CAPITAL LETTER

KEYING MARK



SERIES CODE


LOGO MARK



HSG

CONTACT

RETENTION LEG



18POS(X-KEY) : 1-2040516-9

THIS DRAWING IS A CONTROLLED DOCUMENT:		DWN SEE SHEET 1	 TE Connectivity		
DIMENSIONS:		CHK SEE SHEET 1			
		APVD SEE SHEET 1	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 4-20POS		
		PRODUCT SPEC SEE SHEET 1			
		APPLICATION SPEC SEE SHEET 1			
		WEIGHT -			
MATERIAL		FINISH	SIZE A3	CAGE CODE 00779	DRAWING NO C-2040516
			RESTRICTED TO		
			SCALE 4:1	SHEET 3 OF 3	REV B2