





ROHS



- 4 GND
- 3 D+
- 2 D-
- 1 VBS

MAPX	MODIFICATION	DRW	DATE

特性和 Specifications:

电学 Electrical:

接触电阻 Contact Resistance

30 millionms MAX

耐压 Dielectric Withstanding Voltage:

500v AC AT Sea Level

绝缘电阻 Insulation Resistance:

1000 MEGA ohms MLN

机械 Mechanical:

接合力 Mating Force:

4.0 KG MAX 最大4 Kg

拔出力 Unmating Force:

0.7 KG MIN. 最小0.7 KG

材料 Material:

塑胶 Housing: High Temperature Thermoplastics

UL 94V-V1 PBT

端子 Contact: Copper Alloy 铜合金

铁壳 Shell: Copper Alloy 铜合金

电镀 Finish:

端子 Contact: Plated Gold in Mating Area;

Tin/On Solder Tails

接插点(镀金); 脚镀锡

铁壳 Shell:

nickel Plating 镍镀

产品图 PRODUCT CHART DWG

公差一览表 TOLERANCE UNLESS OTHERWISE SPECIFIED

单位 UNITS

MM

制图 YANQ

制图料号 PRODUCT PART NO. 916-252A1028Y10200

比例 SCALE

1:1

审核 郭治富

产品名称 PRODUCT NO. AF180度15.0直脚有边铜壳PBT黑胶带后塞

日期 DATE

2019-11-07

核准 黄国荣

角法 VER 版本 A0

