





公母对插示意图

NOTES:

SPECIFICATION:

1. CURRENT RATING: 5.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

USB TYPE-C PIN ASSIGNMENTS

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

P/N	(L)	COLOER	额定电流
HC-TYPE C-16P-MM2.4-5A-01	6.50mm	黑色	5A

Ordering Information

HC-TYPE C - 16P - ** - *A - F* - ** - 01

Pin	Type	Current Rated	Foot Length	Colour
4P	TM=Top Mount (板上)	3A	5A	默认:Black
6P	DS=DP+SMT (带后贴)	5A	10A	W=White
8P	MH=Mid Mount (中贴)	5A	10A	B=Blue
12P	CH=Center Mount (中贴)	5A	10A	G=Green
16P	VS=Vertical SMT (直立式)	5A	10A	O=Orange
24P	DP=DP (带后贴)	5A	10A	P=Purple
	CP=Clip (夹板)	5A	10A	Y=Yellow
	FL=Flag (带后贴)	5A	10A	

			GENERAL TOLERANCE	制图	深圳市华灿天禄电子有限公司		
				DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD		
			DIM	TOL	审核	产品名称	TYPE CF 16P 沉板2.4
					CHECK	TITLE	L6.50mm 无柱无弹
			X.X	±0.30	批准	产品料号	版本
			X.XX	±0.20	APPROVAL	PART NO.	REV.
			X.XXX	±0.10	比例		单位
			Angle	±3.0°	SCALE		UNITS
					投影	材料	页次
					Projection	MATERIAL	SHEET
序号	变更内容	日期					
No.	MODIFY CONTENT	MODIFY DATE					

