







ROHS
Compatible

REV (版本)	MARK (标记)	DESCRIPTION (描述)	DATE (日期)	APPROVED (批准)



REFERENCE DRAWING

- SPECIFICATION
1. Rating: DC 12V 50mA Max
 2. Contact resistance: 100mΩ MAX
 3. Insulation resistance: 100MΩ Min
 4. Dielectric strength: 250VAC/min
 5. Operating force: 50gf ± 30gf
 6. Operating life: 100,000 cycles

NO (序号)	PART NAME (部件名)	QTY (数量)	MATERIAL (材料)	REMARK (备注)
5	COVER (盖板)	1	不锈钢	
4	STEM (按钮)	1	PPA	
3	SPRING (弹簧)	1	磷铜	Ag plating
2	HOUSING (底座)	1	LCP	
1	TERMINAL (端子)	1	磷铜	Ag plating
UNSPECIFIED TOLERANCE 未指定的公差				
DRAWN 制图 LUO JIE DATE 日期 2011.10.14 SCALE: 10:1 ITEM 产品类型 DETECTOR SWITCH 检测开关				
CHKD 审核 ROGER LI DATE 日期 2011.10.14 VIEW: 视图 PART NO 型号 YTD-M02-AA				
APVD 批准 ROC ZHAO DATE 日期 2011.10.14 UNIT: mm DWG. NO 图号				

YIYUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO. LTD

UNSPECIFIED TOLERANCE 未指定的公差	TOLERANCE
ANGULAR (角度)	±0.5°
16 < L ≤ 63	±0.4
4 < L ≤ 16	±0.3
L ≤ 4	±0.2