






Circuit Diagram



P.C.B LAYOUT



Specification

Operating Life	10, 000, 000
Contact rating	50mA@12V DC.
Insulation resistance	100MΩ min.
Contact resistance	50mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.3mm
Storage Temperature	- 30° C to 70° C

Type	Operating Force(gf)	High mm	Button	Leads Shape(G, J, T)	Ground pin (0, 1)	Pegs Option(0, 1)
YTSSA001	2:250±30 1:160±30	A: 4.3 B: 7.3	B(Black)	T	0	1 (pegs) 0 (none)

X. ±0.50	X.° ±2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD				
.X ±0.30	.X° ±1°						
.XX ±0.10	.XX° ±0.5°	MAT'L 	PART NO. YTS5A001	TITLE: TACTILE SWITCH 12x12 插脚高寿命			
.XXX ±0.05							
THESE DRAWINGS SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED.COPIED OR USED IN ANYMANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD Email at info@yiyuanswitches.com		FINISH 	APPD: ROGER	DWG NO. : YTS5A001			
			CHKD: ROC				
		Q' TY 	DR: BILLY WANG 2020/08/21	