

KEY FEATURES

- Snap-in LED retention feature simplifies installation by securing the LED to the holder before mounting
- Poke-in wire connection eliminates time consuming soldering to the LED
- Enables constant thermal down force to minimize influence by thermal plastic deformation at high temperature
- Makes easy and clean thermal paste application possible with built-in excess paste overflow feature
- Provides a specified and stable landing area for additional secondary optics
- Optional alternate mechanical optic attachment accessory
- Minimalistic aesthetic design with clear polarity indication to aid assembly
- Mechanically strong and robust design with negligible light interference
- Available optics from Carclo and LEDIL

APPLICATIONS

- Spotlights
- Down Lights
- Stage lights
- Wall washers
- Architectural lighting

LUMAWISE LED Holders

Type Z50 LED holder for Citizen CLL030/032

The TE Solderless LED Holder, Type Z50, is a circular LED holder that provides a quick and easy solderless connection to the Citzen CLL030/032 LED chip on board array family. TE's Type Z50 holder allows the direct attachment of Citizen LEDs to a heat sink using standard screws enabling designs to be easier to use, and faster to market. The Type Z50 reduces assembly costs and provides a quality solderless power connection, secure mechanical attachment, proper thermal hold down forces, and a landing zone with attachment features for additional secondary optics.

MECHANICAL

- Operating temperature range -40 to 105°C
- Utilize a minimum screw size of #4 or M3 for attachment
- Poke-in style electrical contacts supporting 18-22 AWG (0.35 0.75 $\rm mm^2$) solid, fused and stranded wire

5A

- Z50 w/ optics attach: 50mm diameter by 6mm high
- · Z50 low profile: 45mm by 3.4mm high
- Enables compliancy to Zhaga book 3 standard

ELECTRICAL

- Current rating:
- Voltage rating: 300 VDC
- UL1977 and CSA recognized component (cUR)
- IEC 60838-2-2 (up to 60VDC max)

MATERIALS

- High mechanical strength
- High heat resistance
- Good electrical properties
- UL94V-0 flammability rating

PRODUCT OFFERING

Z50 low profile holder:	2213254-1	
Z50 with optic attachment:	2213254-2	
Optional Z50 Reflector Optics Retaining Clips:		
Model 1 for LEDIL optics:	2213194-1	
Model 2 for Khatod optics :	2213349-1	

APPLICATIONS AND SPECIFICATIONS

- Application Specification #: 114-32048
- Product Specification #:
- Product Qualification Report #:



INTELLIGENT BUILDINGS

lumawise.com

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved LUMAVISE, TE Connectivity and TE connectivity (logo) are trademarks. CITIZEN and CITIZEN Micro HumanTech are trademarks or registered trademarks of CITIZEN HOLDINGS CO., LTD. JAPAN Other logos, product and/or company names might be trademarks of their respective owners. USA: 1-800-522-6752 Canada: +1-905-475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666

108-133008

501-19197

France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

1-1773708-9 JG4 PDF 01/2014 HumanTec

Micro HumanTech

PRODUCT DIMENSIONS







Z50 with optic attachment features

Profile	"A"	"B"	TE Part No.
Low Profile	17 mm	3.4 mm	2213254-1
Optics Attach	17 mm	6 mm	2213254-2

TE Holder	Optics Partner	Product	Website	TE Attachment Accessory Required
2213254-2	carclo	NEWTON Series Reflectors	www.carclo-optics.com	None
2213254-2		ANGELA and ANGELINA Series Reflectors	www.ledil.com	2213194-1 (Reflector Optics Retaining Clip Model 1)
2213254-2	Copical Solutions for LED Lighting	LYRA series reflectors	www.khatod.com	2213349-1 (Reflector Optics Retaining Clip Model 2)

Dimensions are shown for reference purposes only. Specifications subject to change. Customer drawing should be used for all design activity.



INTELLIGENT BUILDINGS

lumawise.com

1-1773708-9 JG4 PDF 01/2014

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved LUMAWISE, TE Connectivity and TE connectivity (logo) are trademarks. CITIZEN and CITIZEN Micro HumanTech are trademarks or registered trademarks of CITIZEN HOLDINGS CO., LTD. JAPAN Other logos, product and/or company names might be trademarks of their respective owners.

"B"

USA: 1-800-522-6752 Canada: +1-905-475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

M3 Depth: 4MM MIN

Z50 Low Profile

Ì

Recommended Mounting Hole Pattern

Available Optics