








修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2020-09-18



PCB LAYOUT

Specifications:

- Contact resistance: $\leq 20\text{m}\Omega$
- Insulation resistance: $\geq 500\text{M}\Omega$
- Rated voltage: 100V AC DC
- Rated current: 2.0A AC DC (AWG#24)
- Withstand Voltage: 500V AC/minute
- Temperature Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- Housing: LCP UL94V-0, Natural (Beige)
- Contacts: Phosphor Bronze/Sn-plated
- Solder Tabs: Brass/Sn-plated

孔位	尺寸	A	B	C	孔位	尺寸	A	B	C
2P	7.30	1.50	4.45	9P	17.80	12.00	14.95		
3P	8.80	3.00	5.95	10P	19.30	13.50	16.45		
4P	10.3	4.50	7.45	11P	20.80	15.00	17.95		
5P	11.8	6.00	8.95	12P	22.30	16.50	19.45		
6P	13.3	7.50	10.45	13P	23.80	18.00	20.95		
7P	14.80	9.00	11.95	14P	25.30	19.50	22.45		
8P	16.30	10.50	13.45	15P	26.80	21.00	23.95		

Circuits	DIM. D	DIM. E	Q'ty/Reel	Packing (Reel/Caton)
02~03 PIN	7.5	16	800PCS	20/Reel
04~07 PIN	11.5	24	800PCS	15/Reel
08~11 PIN	14.2	32	800PCS	11/Reel
12~15 PIN	20.2	44	800PCS	8/Reel



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111225 FAX : 0755-29940187

-TOLERANCES- OTHERWISE SPECIFIED 公差参数表						TITLE: 产品名称: 1.5卧贴			
X.X	±0.30	X.X°	±3°	APPD: 核准:	谢亮	PART NO: 产品编号: HDGC1501WRA-S-XP			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对:	王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图:	黄艳兰	2020-09-18	1:1	mm	A018