



TSUSE DATE	2019. 09. 02	OUR P/N	XR6*8-8R2K-长脚
------------	--------------	---------	---------------

1. 外观尺寸图 DIMENSIOIS



2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	$\Phi 0.5$ 2UEW	18 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR6*8-8R2K	8.2uH $\pm 10\%$	30 Ω	1.4A	—	—

备注:

OPERATING TEMP. : -40℃ ~ +85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
洪碧华 2019. 09. 02	关菊花 2019. 09. 02	刘丰 2019. 09. 02	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

MODEL NO: 产品型号:				XR6*8-8R2K-长脚		EVALUATED Q' TY: 试样数:				5PCS	
WATERIAL CODE: 磁材型号规格:				DR6.0*8.0		TESTED DATE: 试制日期:				2019.09.02	
(DATA) 试样情况记录	SPC 规格	L(uH)	DCR(Ω)								
	LOTS 序号	8.2uH±10%	MAX 30								
	1	8.91	23.55								
	2	9.01	23.64								
	3	9.12	23.61								
	4	9.17	24.44								
	5	9.11	23.71								
	6										
	7										
	8										
	9										
	10										
	11										
	12										
REMARK: HM2801A HM2770A HP4342A VR-114 VR115 备注: 1KHz 0.25V 外观.包装: 外套黑色UL套管 500PCS/包, 20000PCS/箱. OK											
RESULTS: 判定:					制样员DRW		东莞市祥如电子				
☒ 合格 (PASSED) ☒ ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____					洪碧华						
					2019.09.02						