





CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2021. 08. 06	OUR P/N	XR5*7-202K-短脚

1. 外观尺寸图 DIMENSIOS



A=5.5MAX
 B=7.9MAX
 C=3.5±0.5
 D=Φ0.60±0.1
 E=2.5±0.5

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	ΦQA-2-0.11线/155℃	298±2	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR5*7-202K-短脚	2.0mH±10%	—	—	—	—

备注:

OPERATING TEMP. : -40℃ ~ +85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
洪碧华 2021. 08. 06	关菊花 2021. 08. 06	刘丰 2021. 08. 06	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:				XR5*7-202K-短脚				EVALUATED Q' TY: 试样数:				30PCS			
WATERIAL CODE: 磁材型号规格:				DR2W 5×7				TESTED DATE: 试制日期:				2021. 08. 06			
(DATA) 试样情况记录	SPC 规格	L(mH) 2.0mH±10%													
	LOTS 序号														
	1	1.9	2.0												
	2	1.9	2.1												
	3	2.0	1.9												
	4	1.9	2.1												
	5	2.1	1.9												
	6	2.0	2.1												
	7	2.1	1.9												
	8	1.9	1.9												
	9	2.1	2.0												
	10	1.9	1.9												
	11	2.1	2.1												
12	2.0	2.0													
REMARK: HM2801A HM2770A HP4342A 备注: 1KHz 0.25V 外观: 外套UL热缩管 OK															
RESULTS: 判定:						制样员DRW				东莞市祥如电子有限公司					
☒ 合格 (PASSED) ☒ ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____						洪碧华									
						2021. 08. 06									