



CUSTOMER		CUSTOMER'S P/S				
TSSUE DATE	2021. 07. 25	OUR P/N	XR8*10-161K-短脚			
1. 外观尺寸图 DIMENSIOS						
		A=10.0MAX B=12.0MAX C=3.5±0.5 D=Φ0.65±0.05 E=5.0±0.05				
2. 接线图 CONNECTION (BOTTOM VIEW)						
						
3. 绕线规格 WINDING SPEC						
端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD			
S---F	Φ0.35 2UEW	70TS (REF)	CLOSED			
4. 电气特性 ELECTRONICS CHARACTERISTIC						
客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz	直流电阻 D.C.R max.	定格电流 I.D.C max.	标识 Marking	规格代码 Sample No.
	XR8*10-161K	160uH±10%	0.33 Ω	0.75A	—	—
备注： OPERATING TEMP. : -40℃ ~ +85℃ INDUCTANCE DROP=10% TYP. AT IDC.						
制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司			
洪碧华 2021. 07. 25	郑菊花 2021. 07. 25	刘丰 2021. 07. 25				



东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号: XR8*10-161K-短脚				EVALUATED Q' TY: 试样数: 10PCS						
WATERIAL CODE: 磁材型号规格: DR 2W8X10				TESTED DATE: 2021.07.25						
D A T A 试 样 情 况 记 录	SPC 规格	L (uH)	DCR (Ω)							
	LOTS 序号	160uH±10%	MAX 0.33							
	1	158	0.264							
	2	162	0.267							
	3	163	0.271							
	4	159	0.266							
	5	165	0.272							
	6	164	0.273							
	7	161	0.268							
	8	161	0.274							
	9	163	0.269							
	10	165	0.273							
	11									
	12									
	13									
14										
REMARK: HM2801A HM2770A HP4342A VR-114 VR115										
备注: 1KHZ 0.25V										
外观: UL外套, OK										
RESULTS: 判定:				制样员DRW		东莞市祥如电子有限公司				
☒ 合格 (PASSED) ☒ ROHS ☐ 非ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____				洪碧华						
				2021.07.25						