






东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO., LTD


CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2022. 05. 05	OUR P/N	XR6*8-331K-长脚

1. 外观尺寸图 DIMENSIOIS



A=7.5MAX
B=10.0MAX
C=17.0±2.0
D=Φ0.65±0.05
E=3.0±0.05

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.18 2UEW	106TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR6*8-331K	330uH±10%	0.98 Ω	320mA	—	—

备注:

OPERATING TEMP. : -40℃ ~ +85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
洪碧华	关菊花	刘丰	
2022. 05. 05	2022. 05. 05	2022. 05. 05	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:				XR6*8-331K-长脚		EVALUATED Q' TY: 试样数:				10PCS	
WATERIAL CODE: 磁材型号规格:				DR6. 0*8. 0		TESTED DATE: 试制日期:				2022. 05. 06	
(D A T A) 试样情况记录	SPC 规格 LOTS 序号	L (uH) 330uH±10%	DCR (Ω) MAX 0.98								
	1	332	0.81								
	2	323	0.83								
	3	321	0.86								
	4	337	0.82								
	5	323	0.88								
	6	324	0.85								
	7	333	0.91								
	8	338	0.84								
	9	331	0.88								
	10	327	0.84								
	11										
	12										
	REMARK: HM2801A HM2770A HP4342A VR-114 VR115 备注: 1KHz 0.25V 外观: 外套黑色UL套管 OK										
RESULTS: 判定:					制样员DRW		东莞市祥如电子有限公司				
☒ 合格 (PASSED) ☒ ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____					洪碧华						
					2022. 05. 06						