




东莞市祥如电子有限公司


DONGGUAN XIANGRU ELECTRONICS CO., LTD

CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2018. 08. 31	OUR P/N	XR4*6-232K-长脚

1. 外观尺寸图 DIMENSIOS (mm)



2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.06 2UEW	340TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR4*6-232K-长脚	2.3mH±10%	19 Ω	60mA	—	—

备注:

OPERATING TEMP. : -40℃~+85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	祥如电子
洪碧华	关菊花	刘丰	
2018. 08. 31	2018. 08. 31	2018. 08. 31	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO.,LTD

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号: XR4*6-232K-长脚				EVALUATED Q' TY: 试样数: 10PCS						
WATERIAL CODE: 磁材型号规格: DR 2UEW4×6				TESTED DATE: 试制日期: 2018.08.31						
(DATA) 试样情况记录	SPC 规格 LOTS 序号	L(uH) 2.3mH±10%	DCR(Ω) MAX 19							
	1	2.25	14.8							
	2	2.28	14.9							
	3	2.24	14.8							
	4	2.26	15.2							
	5	2.25	15.2							
	6	2.25	15.1							
	7	2.28	14.7							
	8	2.23	15.3							
	9	2.27	14.8							
	10	2.25	15.4							
	11									
	12									
REMARK: HM2801A HM2770A HP4342A VR-114 VR115 备注: 1KHZ 0.25V 外观: 外套PVC套管 OK										
RESULTS: 判定: ☒ 合格 (PASSED) ☒ ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____				制样员DRW 洪碧华 2018.08.31		祥如电子				