




TSSUE DATE	2022. 04. 29	OUR P/N	XR8*10-501K-长脚
------------	--------------	---------	----------------

1. 外观尺寸图 DIMENSIOIS



A=9.0MAX


B=11.5MAX

C=13.5±2.0

D=Φ0.6±0.05

E=4.0±0.10

2. 接线图 CONNECTION (BOTTOM VIEW)



3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	2-UEW /155℃ Φ0.25mm	126 TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XR8*10-501K	500uH ±10%	0.9 Ω	—	—	—

备注:

OPERATING TEMP. : -40℃ ~ +85℃

INDUCTANCE DROP=10% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	
洪碧华	关菊花	刘丰	
2022. 04. 29	2022. 04. 29	2022. 04. 29	



东莞市祥如电子有限公司
DONGGUAN XIANGRU ELECTRONICS CO., LTD

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:				XR8*10-501K-长脚		EVALUATED Q' TY: 试样数:				10PCS	
WATERIAL CODE: 磁材型号规格:				DR8.0*10.0		TESTED DATE: 试制日期:				2022.04.29	
(DATA) 试样情况记录	SPC 规格 LOTS 序号	L (mH) 500uH ±10%	DCR (Ω) MAX 3.9								
	1	0.575	0.763								
	2	0.583	0.767								
	3	0.581	0.770								
	4	0.583	0.755								
	5	0.580	0.765								
	6										
	7										
	8										
	9										
	10										
	11										
REMARK: HM2801A HM2770A HP4342A VR-114 VR115 备注: 1KHz 0.25V 外观.包装: 外套黑色PVC套管Φ8, 印字(黑色).											
RESULTS: 判定:				制样员DRW							
☒ 合格 (PASSED) ☒ ROHS ☐ 不合格, 改良后 (FAILED) 参照 (REF) _____				洪碧华							
				2022.04.29							