






N=PIN数



P.C.B LAYOUT

Material 材料

Insulator 塑胶: PA46 PA9T (UL 94V-0)

Contact 端子: Brass 黄铜

Surface Coating 表面镀层: Gold Over Nickel 里镍外金

Electrical Characteristics 电气特性

Current rating 额定电流: 1.0Amps

Dielectric Withstanding Voltage 耐压:

AC 500V for 1 Minute.

Insulator Resistance 绝缘电阻: 1000M Ω Min.

Contact Resistance 接触电阻: 20m Ω Max.

Operating Temperature 工作温度: -40 $^{\circ}$ C ~ +105 $^{\circ}$ C

Max. Processing Temp 瞬时温度:

240 $^{\circ}$ C for 30-60 seconds

(260 $^{\circ}$ C for 10 seconds)

未注尺寸公差			PZ1.27-1xN P		上海洲日电子有限公司					
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD					
	长度	角度			上海康司玛电子设备进出口有限公司					
	X.	±0.3								±5°
	X.X	±0.2								±3°
X.XX	±0.15		版本编号	20171018 A/0	Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD					
制图	周元金	201171018	图纸编号	ZR20171018-227	TEL:86-21-34975176/51571121					
审核	张海娜	201171018	物料编号			1:1		mm	图幅	A4
核准	章妹	201171018	第三视角			:	1		1	