







N=PIN数



P.C.B LAYOUT

Material 材料
 Insulator 塑胶: PA46 PA6T (UL 94V-0)
 Contact 端子: Brass 黄铜
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金
 Electrical Characteristics 电气特性
 Current rating 额定电流: 1.0Amps
 Dielectric Withstanding Voltage 耐压:
 AC 500V for 1 Minute.
 Insulator Resistance 绝缘电阻: 1000MΩ Min.
 Contact Resistance 接触电阻: 20mΩ Max.
 Operating Temperature 工作温度: -40°C ~ +105°C
 Max. Processing Temp 瞬时温度:
 240° C for 30-60 seconds
 (260° C for 10 seconds)

未注尺寸公差			PZ2.0-2xN P		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD 上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD TEL:86-21-34975176/51571121			
尺寸	公差							
X.	±0.3	±5°	版本编号	20171018 A/0	1:1 mm 图幅 A4			
X.X	±0.2	±3°	图纸编号	ZR20171018-242				
X.XX	±0.15		物料编号		: 1 1			
制图	周元金	201171018	第三视角					
审核	张海娜	201171018						
核准	章妹	201171018						