







2.0-3P DT 200mm 26AWG

2.0 mm×3P插头, UL1007, 80 ,26AWG, 线长200mm (1端插头, 另一端剥皮镀锡2mm)



- 1. 极数 poles: 2 to 20P
- 2. 额定电流 Current rating: 2.0A AC, DC
- 3. 额定电压 Voltage rating: 100V AC, DC
- 4. 温度范围 Temperature range: -25. C to +85. C
- 5. 接触电阻 Contact resistance: ≤10mΩ
- 6. 绝缘电阻 Insulation resistance: ≥1000mΩ
- 7. 耐电压 Withstand voltage: 800V AC/minute
- 8. 适用线规 Applicable Wire: AWG #26
- 9. 适用基板厚度 Applicable PC board thickness: 1.6mm

| | |
|-----------------------|-----------------------------|
| 首韩 深圳市首韩科技有限公司 | |
| 日期: 2020-6-15 | 元件名称: 2.0-3P DT 200mm 26AWG |
| 绘制: 李耀凤 | |
| 审核: 钟华华 | |
| 批准: 罗家金 | |
| 尺寸单位: mm | |
| 第 1 页 共 1 页 | |