




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2012.03.13	黃小燕

Specifications

Current Rating:2Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
Contact Material:Phosphor Bronze
Insulator Material:High Temperature Thermoplastic, UL 94V−0 LCP or the equivalent material
All materials must meet Greenconn requirement for environment protection.



Ordering Information


G PFB201 − XX XX A 086 C 1 A X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=Box
C=Tube



格 菱 股 份 有 限 公 司
Greenconn Corporation

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1

GENERAL TOLERANCE	
X.±5.0°	X.±0.30
.X.±3.0°	.X.±0.25
.XX.±2.0°	.XX.±0.15
.XXX.±1.0°	.XXX.±0.10

DESIGN: 黃小燕	DATE: 2012.03.13
CHECKED: 劉北平	DATE: 2012.03.13
AUDITED: 李 輝	DATE: 2012.03.13
APPROVED: cc_li	DATE: 2012.03.13

DWG. NO.	PART NO.
GPFB201−CA86CA	GPFB201−XXXX A086C1AX

TITLE.
2.00 PIN HEADER DUAL ROWS R/A TYPE BASE 2.00H