

F

E

D

C

B

A

F

E




D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
02	△△	變更料號	2008.11.04	彭思城
03	△△	依上級要求變更圖號	2012.01.16	李芳忠



Specifications
Current Rating:2Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:500VAC
Contact Resistance:20mΩMax.
Operating Temperature:-40°C to +105°C
Materials
Contact Material: Brass
Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T or the equivalent material
All materials must meet Greenconn requirement for environment protection.

△△ Ordering Information


G PFB102 - XX XX A 020 B 1 B X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=Box
Selective Packing
C=Tube



格稜股份有限公司 Greenconn Corporation					GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2012.01.16	DWG. NO. △△ GPFB102-CA20BB	TITLE. 2.00 PIN HEADER SINGLE ROW R/A TYPE CONNECTOR
					X.°±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2012.01.16		
					.X°±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2012.01.16		
					.XX°±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2012.01.16		
					.XXX°±1.0°	.XXX±0.10			PART NO. △△ GPFB102-XXXX A020B1BX	
REV. 03	UNIT. mm	SCALE. 5:1	PAGE. 1/1							