




Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS  
Rated Current:1.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:500V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°C to +105°C

Contact Material:Brass  
Contact Plating:Au or Sn Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PC	L
Standard	3.80	2.40	7.20
Alternate			

**Ordering Information**

**PZ 127 - \* - N - Z - \* - \*\***

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type 2-直插 3-贴片 5-插接	Length 产品总长度	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
---	------------------------	------------------------------	-----------------	--

			GENERAL TOLERANCE		制图 DRAWING		<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuaciantianluELECTRONICS CO.,LTD					
			DIM	TOL	审核 CHECK				产品名称 TITLE	版本 REV.	A	
			X.X	±0.30	批准 APPROVAL				产品料号 PART NO.	1.27双排 排针 直针		
			X.XX	±0.20	比例 SCALE				材料 MATERIAL	PZ127-2-N-Z-7.2-XX	单位 UNITS	mm
			X.XXX	±0.10	投影 Projection						页次 SHEET	1/1
1	初版发行		Angle	±3.0°								
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE										