




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2011.03.28	蒙華明



The cap used above 3pin




Specifications
Current Rating: 2Amp
Insulation Resistance: 1000MΩMin.
Dielectric Withstanding Voltage: 500VAC
Contact Resistance: 20mΩMax.
Operating Temperature: -40°C to +105°C
Materials
Contact Material: Phosphor Bronze
High Temperature Thermoplastic, UL 94V-0
LCP or Equivalent Material
All materials must meet Greenncom requirement for environment protection.

Ordering Information

G PFA305 - XX XX A 001 C 1 A X

Recommended P.C.Board
Layout
(Tolerance: ±0.05)



No. of Pins per Row
02~30

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=Box
Selective Packing
C=Tube
E=CAP+Tube
F=CAP+Tape&Reel

格 菱 股 份 有 限 公 司
Greenncom Corporation

REV.	UNIT.	SCALE.	PAGE.		GENERAL TOLERANCE
01	mm	4:1	1/1		X.±5.0° .X.±3.0° .XX±2.0° .XXX±1.0°

DESIGN: 蒙華明	DATE: 2011.03.28
CHECKED: 劉北平	DATE: 2011.03.28
AUDITED: 李輝	DATE: 2011.03.28
APPROVED: cc_li	DATE: 2011.03.28

DWG. NO.	GPFA305-CA1CA
PART NO.	GPFA305-XXXX A001C1AX

TITLE.
2.00 PIN HEADER
THREE ROWS DIP TYPE
CONNECTOR