


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
02	△A	變更料號	2008.10.07	彭恩城
03	△A	依上級要求變更圖號	2012.02.28	李芳忠




2.0 X No. of Positions ± 0.35

2.0 X No. of Contacts — 2.0 ± 0.20

2.00 ± 0.10

2"MAX SWAY
(EITHER DIRECTION)

1.50



PIN 0.50 SQ

2"MAX TOE
(EITHER DIRECTION)

contact end

solder end

3.50 ± 0.20

Ordering Information

G PFA102 — XX XX A 013 A 1 B X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=box
Selective Packing
C=Tube

Recommended P.C.Board

Layout

(Tolerance: ± 0.05)



格 菱 股 份 有 限 公 司 Greenconn Corporation				GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2012.02.28	DWG. NO. △A △A	TITLE. 2.00 PIN HEADER SINGLE ROW DIP TYPE CONNECTOR
X. $\pm 5.0^{\circ}$		X. ± 0.30		CHECKED: 劉北平		DATE: 2012.02.28	PART NO. △A		
.X. $\pm 3.0^{\circ}$		.X. ± 0.25		AUDITED: 李輝		DATE: 2012.02.28	G PFA102-XXXX A013A1BX		
.XX $\pm 2.0^{\circ}$		.XX ± 0.15		APPROVED: cc_li		DATE: 2012.02.28			
.XXX $\pm 1.0^{\circ}$		.XXX ± 0.10							