




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
B	A	變更料號	2009.04.29	彭思城
C	A	變更圖號	2011.07.09	曹 熙

Specifications

Current Rating:3Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:600VAC
Contact Resistance:20mΩMax.
Operating Temperature:−40°C to +105°C
Materials
Contact Material:Brass
Insulator Material: Thermoplastic, UL 94V−0
PBT or the equivalent material
All materials must meet Greenconn
requirement for environment protection.




Ordering Information

G PHA208 − XX XX A 037 A 1 B X

No. of Pins per Row 03~32
Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin
Color 1=Black
Standard Packing
A=Box
C=Tube

Recommended P.C.Board
Layout
(Tolerance:±0.05)



格 菱 股 份 有 限 公 司 Greenconn Corporation				GENERAL TOLERANCE		DESIGN: 曹 熙	DATE: 2011.07.09	DWG. NO. A/△ GPHA208−CA37AB	TITLE. 2.54 PIN AND BOX HEADER DUAL ROW DIP TYPE CONNECTOR
REV. C	UNIT. mm	SCALE. 2.5:1	PAGE. 1/1	X.±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2011.07.09	PART NO. GPHA208−XXXX A037A1BX	
				X.±3.0°	X.±0.25	AUDITED: 李 輝	DATE: 2011.07.09		
				.XX±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2011.07.09		
				.XXX±1.0°	.XXX±0.10				