







ROHS

P.C.B LAYOUT (top view)



DC MATE PLUG

DC-017A



CIRCUIT DIAGRAM

Model No.	1	2	3
PIN	Ø2.0	Ø2.35	Ø2.5

Rating: 1.5A 30V DC
 Contact Resistance: 100 mΩ Max.
 Operating temperature: -20°C ~ 70°C
 Operating force: 3~20N
 Operating Life: 5,000cycles

③	Other Terminal	2	Brass	Sn Plating	
②	Shrapnel	1	Phosphor bronze	Sn Plating	
①	Housing	1	Nylon	Black	
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING
APPROVALS	DATE	HRD 韩宗 ELECTRONICS CO., LTD			
DRAWN	LIUCAN	2023.2.24			
CHECKED					
APPROVALS				PART NO.	DC-017A

TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	±0.20				
	5~10	±0.15	±2°			
	~ 5	±0.10				
				DRAWING NO.		SHEET 1 OF 1

—	A	—	NEW	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE. CHECK. APPRO.