


Technical requirement
技术要求
 1. Rated voltage: 16V (DC)
 1. 额定电压: 16V (DC)
 Rated current: 0.5A
 额定电流: 0.5A
 2. Insulation resistance: ≥ 50M Ω
 2. 绝缘电阻: ≥ 50M Ω

3. Contact resistance: ≤ 300m Ω
 3. 接触电阻: ≤ 300m Ω
 4. Operating force: 35g ± 10g
 4. 操作力: 35g ± 10g
 5. Service life: 30000 times
 5. 寿命: 30000次



6	Tabletting 压片	SUS		
5	Soldering pin 焊线脚	Brass 黄铜	1	Ag plating 镀银
4	Base 底座	PA46	1	Black 黑色
3	Spring 弹簧	Phosphorous copper 磷铜	1	Ag plating 镀银
2	lid 盖子	POM	1	Black 黑色
1	Press handle 按柄	PA9T	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4					COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3			DRAWN BY			FUYUAN	CHECKED BY	COCO	MODEL NO:	TP70611	
A2			DATE			2019	APPROVAL B	ALEN	Https:	www.rocpu.tw	
A1			ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION			ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				