

PCB LAND DIMENSION
PCB电路板焊盘尺寸

SPECIFICATION

规范

Rating: 50mA.12V DC

额定值: 50mA.12V DC

Insulation resistance: 100MQ min.100V DC

绝缘电阻: 100MQmin.100V DC

Dielectric strength: 250V AC for 1 min

介电强度: 250V AC 1分钟

Contact resistance:100mΩ max

Travel: 0.25±0.1mm

行程: 0.25±0.1mm

Lifetime:600000 times



寿命: 600000 times

Operating force:160±50gf

操作力: 160±50gf

Operating temperature rang:-30℃to + 85℃

工作温度范围: -30℃to + 85℃



CIRCUIT DIAGRAM
电路图

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Brown 棕色
1	Cover 盖板	Brass 黄铜	1	
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10721680
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				