








1. Rate voltage: 50mA DC12V
1. 额定电压: 50mA DC12V
2. Contact resistance: $\leq 100\text{m}\Omega$
2. 接触电阻: $\leq 100\text{m}\Omega$
3. Operating force: 260g $\pm$ 50gf
3. 按力: 260g $\pm$ 50gf
4. Travel: 0.20 $\pm$ 0.10mm
4. 行程: 0.20 $\pm$ 0.10mm
5. Insulated resistance: $\geq 100\text{M}\Omega$
5. 绝缘电阻: $\geq 100\text{M}\Omega$
6. Dielectric strength: $\geq 250\text{VAC}$
6. 介电强度: $\geq 250\text{VAC}$
7. Life: 20000times
7. 寿命: 20000次
8. Working temperature: -20 $^{\circ}\text{C}$ ~80 $^{\circ}\text{C}$
8. 工作温度: -20 $^{\circ}\text{C}$ ~80 $^{\circ}\text{C}$



电路图
CIRCUIT DIAGRAM



5	Push-button 按钮	LCP	1	white 白色
4	Bind flange 盖板	Iron cover plate	1	Copper tin plating 镀铜锡
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	LCP	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP12522643
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X					
					ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
					A	B	C	D	E	F	G