





CIRCUIT DIAGRAM



P.C.B LAND DIMENSION



1. Maximum rating: 50mA 12V DC
1.最大额定值: 50mA 12V DC
Minimum rating: 10μA 1V DC
最小额定值: 10μA 1V DC
2. Insulation resistance: $\geq 100\text{M}\Omega$
2.绝缘电阻: $\geq 100\text{M}\Omega$
3. Contact resistance: $\leq 100\text{m}\Omega$
3.接触电阻: $\leq 100\text{m}\Omega$
4. Withstand voltage: 250V AC
4.耐压: 250V AC
5. Operating temperature: $-20^\circ\text{C} \sim +70^\circ\text{C}$
5.使用温度: $-20^\circ\text{C} \sim +70^\circ\text{C}$
6. Action force: $260 \pm 50\text{gf}$
6.动作力: $260 \pm 50\text{gf}$
7. Service life: 1,000,000 times
7.寿命: 1,000,000次
8. Stroke: $0.35 \pm 0.10\text{mm}$
8.行程: $0.35 \pm 0.10\text{mm}$

6	Terminal 端子	BASS 黄铜	4	Ag plating 镀银
5	Housing 外壳	SUS	1	
3	Handle 按柄	silica gel 硅胶	1	Blue 蓝色
2	Shrapnel 弹片	SUS	1	Ag plating 镀银
1	Base 基座	PA46	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP11122631	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
						X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
A		B		C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission