

PCB LAND DIMENSION
PCB电路板焊盘尺寸

SPECIFICATION

规范

Rating: 50mA, 12V DC

额定值: 50mA, 12V DC

Insulation resistance: 100MQ min. 100V DC

绝缘电阻: 100MQmin. 100V DC

Dielectric strength: 250V AC for 1 min

介电强度: 250V AC 1分钟

Contact resistance: 100mΩ max

Travel: 0.25±0.1mm

行程: 0.25±0.1mm

Lifetime: 600000 times



寿命: 600000 times

Operating force: 260±50gf

操作力: 260±50gf

Operating temperature rang: -30℃ to + 85℃

工作温度范围: -30℃ to + 85℃



CIRCUIT DIAGRAM
电路图

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Dark red 暗红色
1	Cover 盖板	Brass 黄铜	1	
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10722650	
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1					ROCPCU TECHNOLOGY CO.,LTD							
REV	DATE	REVISION	DESCRIPTION									ISSUE
						X.X	± 0.15					
					X	± 0.25						
					ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					
A		B		C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission