





CIRCUIT DIAGRAM

1. Rating: DC 12V 50mA
1. 额定值: DC 12V 50mA
2. Contact Resistance: 100mΩ MAX
2. 接触电阻: 最大100mΩ
3. Insulation resistance: ≥ 100M Ω
3. 绝缘电阻: ≥100MΩ
4. Stroke: 0.35 ± 0.10mm
4. 行程: 0.35±0.10mm
5. Service life: 100000 times
5. 使用寿命: 100000 次
6. Operating force: 350 ± 50gf
6. 操作力: 350±50gf
7. Operating temperature: - 20 °C ~ + 70 °C
7. 使用温度: -20℃~ + 70℃



PCB LAND DIMENSION

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 底座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Yellow 黄色
1	Cover 盖板	Brass 黄铜	1	Sn plating 镀锡
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP11013550

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission