



CIRCUIT DIAGRAM

1. Maximum rating: 50mA 12V DC
- 1.最大额定值: 50mA 12V DC
Minimum rating: 10μA 1V DC
最小额定值: 10μA 1V DC
2. Insulation resistance: $\geq 100\text{M}\Omega$
- 2.绝缘电阻: $\geq 100\text{M}\Omega$
3. Contact resistance: $\leq 100\text{m}\Omega$
- 3.接触电阻: $\leq 100\text{m}\Omega$
4. Withstand voltage: 250V AC
- 4.耐压: 250V AC
5. Operating temperature: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 5.使用温度: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$
6. Action force: $260 \pm 50\text{gf}$
- 6.动作力: $260 \pm 50\text{gf}$
7. Service life: 1,000,000 times
- 7.寿命: 1,000,000次
8. Stroke: $0.35 \pm 0.10\text{mm}$
- 8.行程: $0.35 \pm 0.10\text{mm}$



P.C.B LAND DIMENSION



6	Terminal 端子	BASS 黄铜	4	Ag plating 镀银
5	Housing 外壳	SUS	1	
3	Handle 按柄	silica gel 硅胶	1	Blue 蓝色
2	Shrapnel 弹片	SUS	1	Ag plating 镀银
1	Base 基座	PA46	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP11222643
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X					
					ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
					A	B	C	D	E	F	G