



- NOTES:
- Rated voltage: 16V (DC)  
1. 额定电压: 16V (DC)  
Locking voltage: 0.5A  
锁定电压: 0.5A
  - Switch insulation resistance:  $\geq 50M \Omega$   
2. 开关绝缘电阻:  $\geq 50M \Omega$
  - Switch contact resistance:  $\leq 200m\Omega$   
3. 开关接触电阻:  $\leq 200m\Omega$
  - Switch action force:  $20g \pm 5g$   
4. 开关动作力:  $20g \pm 5g$
  - Service life requirements of switch: 20000次循环  
5. 开关的寿命要求:  $\geq 20000$ 次循环

|          |                    |                      |           |                      |
|----------|--------------------|----------------------|-----------|----------------------|
| 6        | Shrapnel<br>弹片     | Silver copper<br>复银铜 | 1         | silver plating<br>镀银 |
| 5        | Welding leg<br>焊脚  | brass<br>黄铜          | 1         | silver plating<br>镀银 |
| 4        | Base<br>底座         | LCP                  | 1         | BLck<br>黑色           |
| 3        | Spring<br>弹簧       | steel wire<br>钢丝     | 1         |                      |
| 2        | lid<br>盖子          | PA46                 | 1         | black<br>黑色          |
| 1        | Press handle<br>按柄 | PA46                 | 1         | BLACK<br>黑色          |
| NO<br>序号 | Part name<br>部件名   | Material<br>材料       | QTY<br>数量 | Remark<br>备注         |

|     |      |          |             |       |
|-----|------|----------|-------------|-------|
| A4  |      |          |             |       |
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



| COMMON TOLERANCE |            |
|------------------|------------|
| X.XX             | $\pm 0.10$ |
| X.X              | $\pm 0.15$ |
| X                | $\pm 0.25$ |
| ANGULAR          | —          |

|   |        |            |      |                      |
|---|--------|------------|------|----------------------|
| UNIT  | MM     | PROJECTED  |      | PRODUCT NAME:        |
| DRAWN BY  | FUYUAN | CHECKED BY | COCO | MODEL NO: TP71122    |
| DATE  | 2019   | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| <b>ROCPCU TECHNOLOGY CO., LTD</b>   |        |            |      |                      |
| Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |        |            |      |                      |