





CIRCUIT DIAGRAM

1. Rating: DC 12V 50mA
1. 额定值: DC 12V 50mA
2. Contact Resistance: 100mΩ MAX
2. 接触电阻: 最大100mΩ
3. Insulation resistance: ≥ 100M Ω
3. 绝缘电阻: ≥100MΩ
4. Stroke: 0.35 ± 0.10mm
4. 行程: 0.35±0.10mm
5. Service life: 100000 times
5. 使用寿命: 100000 次
6. Operating force: 160±50gf
6. 操作力: 160±50gf
7. Operating temperature: - 20 °C ~ + 70 °C
7. 使用温度: -20℃ ~ + 70℃



PCB LAND DIMENSION

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Brown 棕色
1	Cover 盖板	Brass 黄铜	1	Sn plating 镀锡
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10921643
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION								
A		B			C	D	E	F	G		

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission