






NOTES:

1.Rat voltage:50mA DC12V

1.额定电流: 50mA DC12V

2.Contact Resistance:≤100mΩ

2.接触电阻: ≤100mΩ

3.Operating Force:160±50gf

3.按力:160±50gf

4.Travel:0.20±0.10mm

4.行程: 0.20±0.10mm

5.Insulated Resistance:≥100mΩ

5.绝缘电阻: ≥100mΩ

6.Dielectric Strength: ≥250VAC





6.介电强度: ≥250VAC

7.life: 100000 times

7.寿命:100000 次

8.working temperature: -20℃~80℃

8.工作温度: -20℃~80℃



5	Push-button 按钮	Silica gel	1	Bluc 蓝色
4	Blind flange 盖板	Phosphorous copper	1	Copper tin plating 镀铜锡
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	LCP	1	white 白色
1	Card 卡件	Phosphorous copper	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4						UNIT	MM	PROJCTED		PRODUCT NAME:
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP12121625
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—