



PCB.焊接图
PCB.WELDING DRAWING




电路图
CIRCUIT DIAGRAW



NOTES:

- 1.Rating:12VDC 50mA
1.额定值: 12VDC 50mA
- 2.Contact Resistance:≤100mΩ Max
2.接触电阻: ≤100mΩ
- 3.Operating Force:160±50gf
3.操作力: 160±50gf
- 4.Travel: 0.25±0.1mm
4.行程: 0.25 + 0.1mm
- 5.Insulation Resistance:≥100MΩ
5.绝缘电阻: ≥100MΩ
- 6.Dielectric strength: ≥250VAC
6.介电强度: ≥250VAC
- 7.Life: 100,000 times
7.寿命: 100,000 times
- 8.Operating Temperature:-20 ±80℃
8.使用温度: -20 ±80℃



5	Push-button 按钮	PPA	1	white 白色
4	Cover plate 盖片	cutter	1	Copper tin plating 镀铜锡
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	PPA	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP11621625
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				