





CIRCUIT DIAGRAM

1. Rating: DC 12V 50mA
1. 额定值: DC 12V 50mA
2. Contact Resistance: 100mΩ MAX
2. 接触电阻: 最大100mΩ
3. Insulation resistance: ≥ 100M Ω
3. 绝缘电阻: ≥ 100MΩ
4. Stroke: 0.35 ± 0.10mm
4. 行程: 0.35 ± 0.10mm
5. Service life: 100000 times
5. 使用寿命: 100000 次
6. Operating force: 350 ± 50gf
6. 操作力: 350 ± 50gf
7. Operating temperature: - 20 °C ~ + 70 °C
7. 使用温度: -20 °C ~ + 70 °C



PCB LAND DIMENSION

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 基座	PA6T	1	Black 黑色
3	Contact 弹片	SUS	1	Ag plating 镀银
2	Stem 按钮	PA6T	1	Yellow 黄色
1	Cover 盖板	Brass 黄铜	1	Sn plating 镀锡
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP10923560	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
						X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
A		B		C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission