

SJ100645  
(DRAWING NO.)

| 版数<br>REV. | 年月日<br>DATE | DCN NO. | 変更内容<br>DESCRIPTION | 製図<br>DR. | 担当<br>CHK. | 査閲<br>APPD. | 承認<br>APPD. |
|------------|-------------|---------|---------------------|-----------|------------|-------------|-------------|
|            |             |         |                     |           |            |             |             |
|            |             |         |                     |           |            |             |             |
|            |             |         |                     |           |            |             |             |









TABLE 1

| DIMENSION<br>NO. OF<br>CONTACTS (N) | A  | B     |
|-------------------------------------|----|-------|
| 20                                  | 19 | 28.05 |
| 30                                  | 29 | 38.05 |



CABLE ASSEMBLED CONDITION (REF.)  
ケーブル 嵌合状態図 (参考)



MATED CONDITION (REF.)  
嵌合状態図 (参考)

| 3                                  | GROUND PLATE      | 1                                  | COPPER ALLOY      | TIN-PLATING                                   |                                                      |
|------------------------------------|-------------------|------------------------------------|-------------------|-----------------------------------------------|------------------------------------------------------|
| 2                                  | INSULATOR         | 1                                  | GLASS FILLED 4-6N |                                               | UL94 V-0 BLACK                                       |
| 1                                  | CONTACT           | N                                  | COPPER ALLOY      | CONTACT AREA: GOLD (0.1μm MIN) OVER NICKEL    | TERMINAL AREA: (LEAD FREE) TIN/TIN ALLOY OVER NICKEL |
| 符号<br>NO.                          | 名称<br>DESCRIPTION | 個数<br>QTY.                         | 材料<br>MATERIAL    | 仕上<br>FINISH                                  | 備考<br>REMARKS                                        |
| 仕様書 (SPECIFICATION)<br>JACS-1597-* |                   | 第1版 (ORIGINAL DATE)<br>28.Jan.2004 |                   | 尺度 (SCALE)<br>5:1                             |                                                      |
| 公差 (GENERAL TOLERANCE)             |                   | 製図<br>DR.<br>H.SAKURADA            |                   | 名称 (TITLE)<br>FI-X**C<br>-NPB<br>COAXIAL Type |                                                      |
| 寸法 (DIMENSION)                     |                   | 担当<br>CHK.<br>T.YAMAJI             |                   | 重量 (WEIGHT)                                   |                                                      |
| . ±0.8                             |                   | 査閲<br>APPD.<br>M. Suzuki           |                   | 図面番号 (DRAWING NO.)<br>SJ100645                |                                                      |
| .X ±0.4                            |                   | 承認<br>APPD.<br>Y. Miyama           |                   | 版数 (REV.)<br>1                                |                                                      |
| .XX ±0.1                           |                   |                                    |                   |                                               |                                                      |
| .XXX ±                             |                   |                                    |                   |                                               |                                                      |

LEAD FREE この製品は鉛フリー品です