





- NOTES:
1. Rate voltage : 50mA DC12V
1. 额定电压: 50mA DC12V
 2. Contact resistance: $\leq 100m\Omega$
2. 接触电阻: $\leq 100m\Omega$
 3. Operating force: 260g $\pm$ 50gf
3. 按力: 260g $\pm$ 50gf
 4. Travel: 0.20 $\pm$ 0.10mm
4. 行程: 0.20 $\pm$ 0.10mm
 5. Insulated resistance: $\geq 100m\Omega$
5. 绝缘电阻: $\geq 100m\Omega$
 6. Dielectric strength: $\geq 250VAC$
6. 介电强度: $\geq 250VAC$
 7. life: 50000times
7. 寿命: 50000次
 8. Working temperature: -20 $^{\circ}C$ ~80 $^{\circ}C$
8. 工作温度: -20 $^{\circ}C$ ~80 $^{\circ}C$



5	Push-button 按钮	PPA	1	Black 黑色
4	Blind flange 盖板	Cutter	1	Copper tin plating 镀铜锡
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Noumenon 本体	PPA	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP12612650
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				