

Performance Specifications (性能)

<p>Short-time overload 短时间过负荷</p> <p>Soldering heat 耐焊接热</p> <p>Solderability 可焊性</p> <p>Thermal Shock 热冲击</p> <p>Load life 负载寿命</p>	<p>±(0.5%+0.0005Ω)</p> <p>Test method 测试方法: Running under 5 times of rated power in 5 seconds at room temperature. 5 倍额定功率、室温, 持续工作 5 秒 Except for special specifications (see datasheet) (特殊规格除外, 具体详见产品规格书)</p> <p>±(0.5%+0.0005Ω)</p> <p>Coverage must be over 95%.</p> <p>±(0.5%+0.0005Ω)</p> <p>±(1%+0.0005Ω)</p>
---	--

Ordering Procedure (Example:LR12 2W 1% 5mΩ T/R-4000)

订购方式 (例如: LR12 2W 1% 5mΩ T/R-4000)

