



4805 (3/|3)




THIS DRAWING IS	A
DIMENSIONS:	
mm	
material SEE CALLOUT -	
	DIMENSIONS: mm MATERIAL


2		

		REVISIONS			
Р	LTR	DESCRIPTION	DATE	DWN	APVD
		INITIAL DRAWING	24MAY2019	JMS	GK
	А	INITIAL RELEASE	04DEC2019	CN	GK





ISOMETRIC VIEWS SCALE 4:I



		G R A	λΥ	NA	D	2356394-8
		GRE	ΕN	NA	С	2356394-7
		BLU	JE	NA	В	2356394-6
		NATURAL	(BROWN)	NA	A	2356394-5
		G R A	λΥ		D	2356394-4
		GRE	ΕN		С	2356394-3
		BLU	JE		В	2356394-2
		NATURAL	(BROWN)		А	2356394-1
		HOUSING	COLOR	C P A Q T Y	KEYING OPTION	PART NUMBER
A CONTROLLED DOCUMENT.	dwn J.SHIRK chk G.KITAZA	24MAY2019 24MAY2019		-E TE	TE Co	nnectivity
$\begin{array}{c} \text{TOLERANCES UNLESS} \\ \text{OTHERWISE SPECIFIED:} \\ \hline \\ 0 \text{ PLC } \pm 1 \\ 1 \text{ PLC } \pm 0.3 \\ 2 \text{ PLC } \pm 0.15 \\ 3 \text{ PLC } \pm 1 \end{array}$	24MAY2019 WA		ASSEMBLY N, I.2mm	MCON		
4 PLC ±- ANGLES ±1°	APPLICATION S		SIZE CAGE C	_		RESTRICTED T
FINISH -	WEIGHT	-	A     -	C = 2356	6394	
-	RESTRICTE	D CUSTOMER	-	S	CALE 8 ·   SHEE	T OF REV A

В