









ROHS



P1 视图

Terminal	①	②	③	④	⑤	⑥
Direction						
↓		●			●	
↖	●				●	
↗				●	●	
↙			●		●	
↘					●	●

Circuit Diagram



PCB Layout(Pattern Side)

NOTE:
Operating Force:
lever portion: 170 ± 35 gf
Push portion: 350gf
Travel: 4-direction 5°±2°
center push 0.20±0.1mm

⑦	Mylar	—	1	Natural	—	—
⑥	Contact 1	—	—	F.Ag/SUS	—	—
⑤	Terminal	—	6	Brass(0.15t)	Plating silver	—
④	Base	—	1	LCP	Black	—
③	Cover	—	1	SUS	—	—
②	Axle sleeve	—	1	LCP	Black	—
①	Keystoke	—	1	PA46	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		HRO韓泰® ELECTRONICS CO.,LTD		
DRAWN	LIUCAN		2022.11.9				
CHECKED					TITLE:	1.95*1.95重克力高度5.0MM	
APPROVALS					PART NO.	K1-5203UA-06	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.	_____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.