







ROHS



3D VIEW




P.C.B LAYOUT
TOP VIEW



NOTES:

1. REQUEST OF THE SPECIFICATION:

- 1.1 CONTACT CURRENT RATING: 1A.;
- 1.2 CONTACT RESISTANCE: 100 mΩ MAX.;
- 1.3 INSULATION RESISTANCE: 100MΩ MIN.;
- 1.4 DIELECTRIC WITHSTANDING: 500V AC MIN.;
- 1.5 DURABILITY: 5,000 CYCLES MIN.;
- 1.6 CONNECTOR MATING FORCES: 30N MAX.;
- 1.7 CONNECTOR UNMATING FORCES: 3N MIN.;



③	Other Terminal	_____	4	SUS	Au Plating	_____		
②	Terminal 2#4#	_____	2	Copper Alloy	Au Plating	_____		
①	Housing	_____	1	LCP	Black	_____		
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK		
APPROVALS			DATE	HRO 皓龙® ELECTRONICS CO.,LTD				
DRAWN	LIUCAN	2023.2.28						
CHECKED			TITLE:				PHONE JACKES	
APPROVALS			PART NO.				PJ-399Q	
D.	TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
		10~30	±0.20					
		5~10	±0.15					
		~ 5	±0.10					
		±2'		DRAWING NO.	_____	SHEET 1 OF 1		

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.