

## CSNE151-204

( [Home](#) : [Products](#) : [Sensors](#) : [Current Sensors](#) : [Closed Loop](#) : [CSN](#) )



CSN Series closed loop current sensor, measures ac, dc or impulse current, 50 amp-turns nominal,  $\pm 90$  amp-turns range, miniature housing, 2000 turn

Actual product appearance may vary.

### Product Specifications

Product Type	Closed Loop Linear
Sensed Current Type	ac or dc
Sensed Current Range	$\pm 90$ A
Package Type	Series Connect PCB Mount
Output Type	Current
Continuous Current	$\pm 50$ A
Operate Current	50 A RMS @ 25 °C
Supply Current	$\pm 12$ mA + Output
Supply Voltage	$\pm 15.0$ Vdc
Offset Current	$< \pm 0.3$ mA
Offset Current Drift	$< \pm 0.6$ mA
Coil Resistance	190 Ohm
Response Time	$< 1$ $\mu$ s
Coil Turns	2000
Output Nominal	25 mA
Operating Temperature	-40 °C to 75 °C [-40 °F to 167 °F]
Storage Temperature	-40 °C to 90 °C [-40 °F to 194 °F]
Measuring Resistance	0 Ohm min., 250 Ohm max.
Housing Material	Glass-filled PBT (UL94-V0)
Mounting	PCB on 9 Pins
Pinout Style	4 Pin
Accuracy	$\pm 0.5$ %
Availability	Global
Comment	Low cost miniature 50 A sensor.
UNSPSC Code	41111928
UNSPSC Commodity	41111928 Current Sensors
Series Name	CSN