



CASE ASSEMBLY FOR REFERENCE



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05



G-Switch USB-C Specification:

- Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- Voltage rating: 24V AC
- Withstanding voltage: 100V AC/minute
- Contact resistance: 40mΩ Max
- Insulation resistance: 100MΩ Min
- Operating temperature: -40°C ~ +85°C
- Mating force : 5N~20N
- Unmating force: 8N~20N
- Durability cycle: 10,000 cycles
- Waterproof grade: IP-X8

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

1	COVER SHELL	STAINLESS STEEL	NI PLATED
2	SHEATH	HIGH TEMPERATURE PLASTIC	Black UL 94 V-0
3	MID PLATE	STAINLESS STEEL	NI PLATED
4	HOUSING	HIGH TEMPERATURE PLASTIC	Black UL 94 V-0
5	TERMINALS	COPPER ALLOY	Au PLATING ON CONTACT AREA
NO.	PARTS	MATERIAL	REMARKS

SCALE: 1:1	UNIT: mm	Title: Horizontal Type-c 16P Female SMT CH=2.39 L=7.85mm	
SIZE: A4		Molde Code: GT-USB-7070C	
Unless otherwise General Tolerance:		DRAWN	CHECKED
X.	±0.20	Xia	Chen
X.x	±0.15	APPROVED	DATE
X.xx	±0.10	Chen	2023.02.01
X.xxx	±0.05		
Angles	±3°		



REV: A0 SHEET: 1/1